



Product Code . EL-EELE-11367

Sieve Plate Distillation Column

Description

Sieve Plate Distillation Column

The vapors from the top of column are condensed in the shell and tube type condenser by circulating cooling water supplied by laboratory overhead tank. An electrically heated re-boiler is installed at the bottom of the column. The bottom product is collected in the tank. The condensate is divided into reflux and distillate by automatic reflux divider and R/D Ratio can be varied. Instrumentation is done for pressure & temp. Reflux is fed back to the column and distillate is received in a receiving tank. The column is made of Stainless Steel material with seven sieve trays. The complete column is insulated for minimizing the heat loss.




Features:-

- Water Supply 2 LPM at 5 m head.
- Stainless Steel tanks and wetted parts.
- Electricity Supply: 1Phase, 220 V AC, 6.5 kW.
- Superb Painted structure.
- Simple to operate & maintain.
- Compact & stand alone set up.
- Utilities Required.
- Drain.

-
- Required Chemicals.
 - Refractrometer for analysis.

We are leading manufacturers, suppliers of Sieve Plate Distillation Column for Electronics Engineering Lab Equipments. Contact us to get high quality Sieve Plate Distillation Column for Electronics Engineering Lab Equipments for schools, colleges, universities, research labs, laboratories and various industries.

```
{ "@context": "https://schema.org/", "@type": "Product", "name": "Sieve Plate Distillation Column",  
"image": "http://www.educational-  
equipments.com/images/catalog/product/709505191SievePlateDistillationColumnWithlogo.jpg",  
"description": "The vapors from the top of column are condensed in the shell and tube type  
condenser by circulating cooling water supplied by laboratory overhead tank. An electrically heated re-  
boiler is installed at the bottom of the column. The bottom product is collected in the tank. The  
condensate is divided into reflux and distillate by automatic reflux divider and R/D Ratio can be  
varied. Instrumentation is done for pressure & temp. Reflux is fed back to the column and distillate is  
received in a receiving tank. The column is made of Stainless Steel material with seven sieve  
trays. The complete column is insulated for minimizing the heat loss. Features:- • Water Supply 2  
LPM at 5 m head. • Stainless Steel tanks and wetted parts. • Electricity Supply: 1Phase, 220 V AC,  
6.5 kW. • Superb Painted structure. • Simple to operate & maintain. • Compact & stand alone set up.  
• Utilities Required. • Drain. • Required Chemicals. • Refractrometer for analysis. We are leading  
manufacturers, suppliers of Sieve Plate Distillation Column for Electronics Engineering Lab  
Equipments. Contact us to get high quality Sieve Plate Distillation Column for Electronics Engineering  
Lab Equipments for schools, colleges, universities, research labs, laboratories and various  
industries.", "brand": "Educational Lab Equipments", "sku": "5", "gtin8": "5", "gtin13": "5", "gtin14": "5",  
"mpn": "5", "aggregateRating": { "@type": "AggregateRating", "ratingValue": "5", "bestRating": "5",  
"worstRating": "0", "ratingCount": "15" } }
```

Educational Lab Equipments,
#449, HSIIDC, Industrial Area, Saha, Haryana
Direct Contact Details  +91-98173-19615  sales@educational-equipments.com
 www.educational-equipments.com